

MICROMASTER 4 COMMUTATING CHOKE 380-600 V 3AC 151 A  
STAND ALONE FSF - 0.15 MH




Figure similar

Order number	6SE6400-3CC11-2FD0
Phase number / of the input voltage	3
Type of voltage / of the input voltage	AC
Input voltage	380 ... 480
Output current / Rated value	151 A
Active power loss	
• at 50 Hz	Wert fehlt!
• at 60 Hz	Wert fehlt!
Type of electrical connection	
• for mains supply line	Flat connector for cable lug M10
• for load-side outgoing feeder	flat connector for cable lug M10
Type of connectable conductor cross-section / for load-side outgoing feeder	Wert fehlt!
Type of electrical connection / for PE conductor	M8 screw studs
Protection class IP	IP00
Width	240 mm
Height	228 mm
Depth	141 mm
Net weight	25 kg
Certificate of suitability	cURus

### Further information

#### Information und Download Center

[https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order\\_form.aspx](https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order_form.aspx)

#### Technical documentation

<http://w3.siemens.com/mcms/mc-solutions/en/motion-control/support/technical-documentation/Pages/technical-documentation.aspx>

#### Industry Mall

<https://eb.automation.siemens.com/mall/en/WW/Catag/Product/6SE64003CC112FD0/all>

