

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731100038](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Standard-Density Waterproof D-Sub Connector, Male, Straight, Solder Cup, Gold over Nickel Phosphorus Plating, Front Panel Mount, Plastic Watertight Frame, 25 Circuits

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	D-Sub Products
Series	173110
Datasheet Order No	987652-0111
Exclude SD Check	Yes
IP Rating	IP67
Overview	FCT D-Sub Connectors
Product Category	D-Sub Connector
Product Name	FCT Products
Type	Standard Density
UPC	889056487078

Physical


Circuits (Loaded)	25
Circuits (maximum)	25
Color - Resin	Red
Durability (mating cycles max)	500
Gender	Male
Material - Contact	Copper Alloy
Material - Resin	PBT
Material - Shell	Brass
Net Weight	18.000/g
Number of Rows	2
Orientation	Straight
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Panel Mount	Front
Panel Mount Method	Thread-In
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Contact	Gold over Nickel Phosphorus
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shielded	Yes
Temperature Range - Operating	-25° to +70°C
Termination Style	Solder Cup
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Wire Size AWG	20

Electrical

Current - Maximum per Contact	7.5A
-------------------------------	------

Material Info

Engineering Number	FWDF25PA
--------------------	----------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[173110 Series](#)

Mates With

FCT Standard-Density D-Sub, Size 3, 25 Position, Socket

Use With

FCT D-Sub Dust Caps

This document was generated on 06/21/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION