

CONSTANT VOLTAGE LED DRIVER

24VDC 150WATT



POWERPAX: LED-DR-24V-150W-IP67

Features:

- Input Voltage 180-264vac
- IP20 Rated
- Low Profile
- Compact Plastic Low Profile enclosure
- 1 Year Warranty



Description:

The Range of 150 Watt Constant Voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications.

Specification	
Part Number	LED-DR-24V-150W-IP67
Output Voltage Rating	24vdc
Output Current Range	0-6.25A
Rated Power	150 Watt
Dimensions	190 (l) x 61.5 (w) x 36.5 (h) mm
Input Voltage Range	200-277VAC
Input Voltage Frequency	50-60Hz
Inrush Current	<75A
input power	>0.9A
Efficiency	90%
Power Consumption Without Load	<0.50W
Overload Protection	Ta ,0.94-1.06 times of input voltage, 1.2 times of rated power
Short Circuit Protection	Ta ,0.94-1.06 times of input voltage
Automatically Restart	Yes
Working Temperature	-40°C ~ +60°C
Relative Humidity	45% ~ 85%
MTBF	30000hr
EMI emission	EN55015
EMS Standards	EN61000-4-2,3,4,5,6; EN61547
Safety Standards	EN61347-1, EN61347-2-13

POWERPAX

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

CONSTANT VOLTAGE LED DRIVER

24VDC 150WATT

POWERPAX: LED-DR-24V-150W-IP67

Diagrams



Wiring Diagram

