



### Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial   |
| Product name                | Spacial S3DEX                                   |
| Application                 | ATEX certified application                      |
| Category                    | Compact enclosure                               |
| Enclosure nominal height    | 15.75 in (400 mm)                               |
| Enclosure nominal width     | 11.81 in (300 mm)                               |
| Enclosure nominal depth     | 7.87 in (200 mm)                                |
| Door type                   | Solid   |
| Mounting plate description  | Without mounting plate                          |
| Type of gland plate         | Without gland plate                             |
| Installation accessory type | Wall-mounting                                   |
| Product destination         | For potentially explosive atmosphere            |
| Device composition          | 1 door<br>1 lock<br>Body with clamped blind nut |

### Complementary

|                             |   |
|-----------------------------|---|
| Body type                   | Gutter-shaped front rail double sheet thickness<br>Single piece body      |
| Number of doors             | Front face: 1 door(s)   |
| Door opening side           | Reversible 120 °)   |
| Lock type                   | Double-bar lock   |
| Accessibility for operation | Front   |
| Removable parts             | Door by hinges  |
| Material                    | Steel   |
| Surface finish              | Epoxy-polyester powder  |
| Color                       | Gray RAL 7035)  |
| Standards                   | EN 60079-0:2012<br>EN 60079-7:2007<br>EN 60079-31:2009                    |
| Marking                     | II 2 GD Ex e IIC Gb Ex tb IIIC Db according to the ATEX directive 94/9/EC |
| Net weight                  | 12.70 lb(US) (5.76 kg)  |

### Environment

|                         |   |
|-------------------------|---|
| IP degree of protection | IP66 IEC 60529 enclosures with single door) |
| IK degree of protection | IK10 IEC 62262                              |

### Ordering and shipping details

|                       |  |
|-----------------------|--|
| Category              | 80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL |
| Discount Schedule     | ES1  |
| GTIN                  | 03606480158650                             |
| Nbr. of units in pkg. | 1  |
| Package weight(Lbs)   | 12.67 lb(US) (5.75 kg)                     |
| Returnability         | No   |
| Country of origin     | FR   |

## Packing Units

|                        |                    |
|------------------------|--------------------|
| Unit Type of Package 1 | PCE                |
| Package 1 Height       | 12.52 in (31.8 cm) |
| Package 1 width        | 9.76 in (24.8 cm)  |
| Package 1 Length       | 16.26 in (41.3 cm) |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|