

## CKJN clamp holder, negative, left

For copy, longitudinal and face turning with KNUX indexable insert

**ATORN**<sup>®</sup>

### Application


For copy, longitudinal and face turning with KNUX indexable insert, 55°

### Version

- Precision-manufactured steel support, burnished, hardened, adjustable clamp, type K, working angle 93°, tip angle 55°, clearance angle 0°

### Advantage

- For copy, longitudinal and face turning particularly on low-performance machines
- Positive cutting geometry of the indexable insert ensures low cutting forces
- Broad range of use: suitable for both finishing and roughing operations



<b>Art. No.</b>	<b>17825 011</b>
<b>ISO name</b>	CKJN R/L 2020 K16
<b>Shaft height</b>	20 mm
<b>Shank width</b>	20 mm
<b>Length</b>	125 mm
<b>Length of head</b>	34 mm
<b>Programming size</b>	30 mm
<b>Suitable for indexable inserts</b>	KNUX 1604..
<b>Tool design</b>	Left
<b>DIN</b>	4983

### EAN-Code

4050293127157