

Adjustable clamps

With stepped teeth



Version:

- Heat-treated steel
- Painted
- With stepped teeth
- Only in conjunction with packing blocks, no. 26150-26151



Art. no.	26136 035
Slot width	11 mm
Length	125 mm
Suitable cheese-head screw DIN 912	M10
Slot length	70 mm
Clamping shoe height	15 mm
Clamping shoe width	30 mm
Width 3	12 mm
Length 2	15 mm
DIN	6314

EAN-Code

4020772070236