

Clamp thermometer with smart phone operation

Model testo 115i



Application:

Clamp thermometer with smart phone operation, for measurements on pipes with a diameter from 6 to max. 35 mm. Ideally suited as a temperature measuring instrument for servicing and troubleshooting refrigeration, air conditioning and heating systems as well as for installing them. Trouble-free use at entirely separated measuring points with a Bluetooth® range of up to 100 m.

Advantage:

- Compact professional measuring instrument from the Testo Smart Probes range for use with smart phones/tablets
- Measurement of the feed and return temperature of heating systems
- Temperature measurement on refrigeration systems for calculating overheating and under-cooling
- Rapid detection of temperature changes by graphical process display
- Analysis and transmission of measured data via testo Smart App

Delivery:

Clamp thermometer testo 115i, batteries and calibration log.



Art. no.	46105 500
Brand	TESTO
Manufacturer Part Number	0560 2115 02
Model	testo 115i
Min./max. temperature measuring range	-40 to 150 °C
Accuracy temperature	+/- 1,3°C at -20 to +85°C
Digit increment (measuring instrument for temperature)	0.1 °C
System requirement	At least iOS 11 or newer, At least Android 6 or newer, At least Bluetooth 4.0
Length x width x height	183 x 90 x 30 mm
Compatible with	Sensor type NTC
Coverage distance	100 m
Min./max. operating temperature	-20 to 50 °C
Number of rechargeable batteries/batteries	3 PCS
Battery designation	Micro AAA; R03; UM4
Weight of rechargeable battery/battery	0.012 kg
Rechargeable battery/battery capacity	1.2 Ah
Battery voltage	1.5 V
Type of rechargeable battery/battery	AlMn
Gross Weight	0.285 kg
Product Group	4CF

EAN

4029547022487