

## Flow meter (anemometer)

**ORION**<sup>®</sup>

### Application:

For simple measurements of air-conditioning ventilation systems.

### Version:

- Running display
- Max-hold display
- AVG display (average value)
- Switch between units of display: m/s, km/h, ft/min., MPH, knots
- Energy-saving Auto-OFF function

### Advantage:

- Handy device size and easy one-hand operation
- Automatic display illumination with brightness sensor
- Large digits for clear view of measured values

### Delivery:

Battery (1x 9 V block battery, type 6 LR 61)



<b>Art. no.</b>	<b>46210 020</b>
<b>Min./max. current of measuring range</b>	0.4-25 m/s
<b>Digit increment, current</b>	0.01 m/s
<b>Current error limit (+/-)</b>	0.45 m/s
<b>Rechargeable battery/battery capacity</b>	550 mAh
<b>Battery voltage</b>	9 V
<b>Type of rechargeable battery/battery</b>	AlMn
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Min./max. working temperature</b>	0 to 40 °C

### EAN-Code

4039247962242