

DN7.2 standard steel coupling

in accordance with ISO 6358

ATORN[®]

Version

- check valve in the clutch, forcibly unlocked when coupling. plug without a check valve.
- sliding sleeve to 8 bar, easy to operate with one hand.
- material:
- coupling: steel
- connector: galvanised steel
- seals: NBR
- springs: spring steel
- rollers: Niro steel

Advantage

- robust and therefore ideal for heavy-duty use



Art. No.	75423 470
Type	with hose nozzle
DN nominal width	DN 7,2
Inner hose diameter	10 mm
Flow capacity	1300 l/min
Max. working pressure	16 bar
Min. working pressure	1 bar
Length	57 mm
Width across flats	10 mm
Min./max. temperature resistance	-10 to 90 °C
Material	Steel

EAN-Code

4050293533620