

Cover for Holder OGD, OGD-SMD



4W/10A



### Standards

- IEC 60127-6
- UL 4248-1 / UL 512
- CSA C22.2 no. 39

### Approvals

- VDE Certificate Number: 4008993
- UL File Number: E39328

### References

Mating cover to [OGD](#); [OGD-SMD](#)

### Weblinks


[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Packaging details](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

### Technical Data

Fuse-Link	6.3 x 32mm
Rated Power Acceptance IEC	4W / 10A @ Ta 23°C
Admissible Ambient Air Temp.	-40°C to 85°C
Material: Cover	Thermoplastic UL 94V-0
Storage Conditions	0°C to 60°C, max. 70% r.h.

Soldering Methods	Reflow, Wave <a href="#">Soldering Profile</a>
Solderability	245 °C / 3 sec acc. to IEC 60068-2-20, Test Td
Resistance to Soldering Heat	260 °C / 10 sec acc. to IEC 60068-2-20, Test Td
Contact Resistance	< mΩ at 20 mV

### Dimension



### All Variants

Description	Order Number
Reflow-Cover	0853.0917

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/Stock-Check/Stock-Check-SCHURTER>

### Packaging Unit

Bulk (100 pcs.)