


PCE data sheet

article#	2355-6
article description	CEE-connector 63A 5p 6h IP67 pilot contact POWER TWIST
description long	CEE-connector 63A 5p 6h IP67 POWER TWIST housing material: PA6 rated current: 63A number of poles: 5 (3P+N+PE) clock-position: 6h rated voltage/frequency: 200/346V~ - 240/415V~ / 50+60Hz contacts: brass, with lamellar spring (CuBe) connection technology: frame terminals with screws IP protection class: IP66/IP67 Extra: pilot contact with screw terminal (rated current 2A)
GTIN (EAN)	9003399197833
country of origin	AT
customs number	85366990
packaging quantity	2
minimum order quantity	2



ETIM 7.0	EC001320
IEC-amperage	63 A
Number of poles	5
Voltage acc. EN 60309-2	400 V (50+60 Hz) red
Clock hour position	6 h
Identification colour	Red
RAL-number	7046
Degree of protection (IP)	IP67
Connection system	Screwed terminal
Angle of plug	Straight
Cable entry	Swivel
Material	Plastic
Contact material	CuZn
Surface finish contacts	Untreated



a	269 mm
b	114 mm
K (cable Ø)	14,5-36 mm
SW	61 mm
wire flexible	6-16 / 1-2,5 (pilot contact) mm ²
contact screws	200 / 100 (pilot contact) Ncm
strain relief	1500 Ncm
dismantling length	100 mm
stripping length	15-18 mm



www.manufacturer-safety.info