



**SVS ECO VALVE PLUG FORM A 18MM 230V**

3+PE field-wireable M16x1.5

Form A (18 mm) for pressure switch  
0...230 V AC/DC, without components  
metric

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Height: 31 mm

Product may differ from Image

### Approvals



### Form

29405

### Technical Data

Operating voltage	0...230 V AC/DC
Operating current per contact	max. 10 A
Connection cross section	0.5...1.5 mm <sup>2</sup>
Sealing range (cable diameter)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Contact figure	Cable outlet can be turned in 90° steps
Compression gland	M16 × 1.5 mm
Protection	IP65 inserted and tightened

### General data

Temperature range	-40...+80 °C
-------------------	--------------

### Commercial data

country of origin	HU
customs tariff number	85369010
minimum order quantity	1