

## Accessory

LASER-LPG-PACKAGE  
Order Number: 70144352

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-20		40	°C
Storage Temperature	-50		50	°C

## Optical Parameters

LB Rating	180-315 D LB7 + IR LB4, 315-532 DIRM LB6, 615-660 DIR LB3, 630-711 DIR LB5, 648-708 D LB5+IR LB6, 654-699 D LB5+IR LB8, 665-715 D LB4+IR LB5, 694 IR LB7, 720-1100 DIRM LB5, 775-1085 D LB5+IRM LB6, 790-1080 D LB6+IRM LB7, 950-1085 DIRM LB6
Lens Color	Aqua, Blaugrün, Grün, Orange

## Mechanical Parameters

Material	Plastic
Weight	500 g


(\*) Over the complete operating temperature range

## Features




- Four laser glasses for different wavelengths
- Incl. wall holder
- Stickers with mandatory and hazard sign

## Picture



## Safety Label



## Valid Revision

| 17-NOV-2020