


Table:

| L | DRAWING P/N: | CUSTOMER P/N: | CTN/Packing Q'ty |
|-----------|--------------|---------------|------------------|
| 500±15mm | CAC250059 | PSG03556 | 220PCS |
| 1000±20mm | CAC250060 | PSG03557 | 120PCS |
| 1500±20mm | CAC250061 | PSG03558 | 90PCS |
| 2000±30mm | CAC250063 | PSG03559 | 60PCS |
| 3000±30mm | CAC250064 | PSG03560 | 50PCS |
| 5000±30mm | CAC250065 | PSG03561 | 40PCS |

Pin Assignment



Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm Max
3. Insulation Resistance: 10M ohm Min
4. Hi-Pot: 100V DC/10ms

| NO | DESCRIPTION | Q'TY | UNIT |
|----|---|------|------|
| 10 | Display Port Transparent Dust Cover | 2 | pcs |
| 9 | Inside Molding:PE | 3 | g |
| 8 | Outside Molding:45P PVC Color:Black | 6 | g |
| 7 | H.S.T:Ø1.5*5mm Black | 10 | pcs |
| 6 | H.S.T:Ø1.0*10mm Black | 10 | pcs |
| 5 | H.S.T:Ø2.5*15mm Black | 10 | pcs |
| 4 | Display Port ABS Shell Color: Black | 2 | pcs |
| 3 | Display Port ABS Shell Color: Black | 2 | pcs |
| 2 | Display Port Male Pin Gold,Insulation Black,Shell Nickel Plated | 2 | pcs |
| 1 | Display Por UL20276 (7/0.127TA*1PR+EAM)*5PCS+7/0.127TA*5C+AEB OD:7.3MM Color:BLACK | L | m |