

60mm Compact fan



- With electronic protection against reverse polarity. The fan only operates when the polarity is correct. Impedance-protected against locked rotor and overloading.
- Fan of fibreglass reinforced plastic. PBT housing, PA impeller
- Air exhaust over struts. Rotational direction CCW looking at rotor
- Fitted with 3 pin molex connector (22-01-2035)
- Sensor signal for speed monitoring

Part Number	Air flow @ free air		Nominal voltage	Voltage Range		Noise	Sinter-sleeve Bearings	Power input	Nominal speed	Temperature range	Service life L ¹⁰ @20°C/ at 60°C	Dimension A	Dimension B
	m ³ /h	CFM		VDC	VDC								
612F/2L-640	15	8.8	12	10.8...13.2	11	Yes	0.28	2250	-20...+85	50,000/20,000	15	308	
612F/2-638	27	15.9	12	10.8...13.2	27	Yes	1.0	3900	-20...+75	50,000/20,000	15	308	
612N/2GML-096	23	13.5	12	8...15	19	Yes	0.9	3000	-20...+70	80,000/50,000	25	318	

subject to alterations

Dimensions

