# Lamp Holder

Features

- Screw mount 12mm centres
- Rear Cable Entry
- The method of wiring must be such that no stress or bending motions will be transferred to the contacts, thus reducing the contact / pressure on the lamp pins

Specifications

T-Marking	: 250
Connection	: Cable PTFE, rear cable entry
Housing	: Housing ceramic
Rating	: 10 A / 50 V
Housing	: Ceramic
T 250 for the contacts (material Ni)	
Wires	: Cu, nickel plated, 1mm^2,
Insulation	: PTFE (maximum 250°C), with ferrule
Free Cable Length	: 140 mm

Diagram

Dimensions : Millimetres

Part Number Table

Description	Part Number
Lamp Holder, Dicr, GU5.3	25.105.3101.00

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO