

IN 30 5

Screwdriver bit socket 3/8"

for in-hex screws, long pattern

Code	ETIM
6241280	ECO02157 Innensechskant-Einsatz für Steckschlüssel
EAN	UNSPSC
4010886624128	27-11-17-01 Schraubendreher
Country of Origin	eCl@ss
Germany	21-04-04-02 Schraubendrehereinsatz
Customs tariff no.	
82079030	



Article description

- Square drive as per DIN 3120 - C 10, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- Chrome-plated
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated
- * not standardised

Article information

Contents (Qty of pieces)	1 tlg.	Drive connector square female (metric)	10,0 mm
Total length [mm]	47 mm	Total width [mm]	17,5 mm
Net weight [kg]	0,039 kg	Drive connector square female [inch]	3/8"
Material	Chrome-vanadium steel	Tip length	19,0 mm
Width across flats 1 [mm]	5	Standard	DIN 7422 DIN 3120 - C 10 ISO 1174
Surface	chrome-plated	Insert Ø Actuator	17,5 mm
REACH registration available	0		