

## Profile Shallow Wide Surface 30

Profile Shallow Wide Surface 30 CDE-9/T 2m anodised  
0022600



### Product features

- A shallow wide 1000mm length anodised aluminium lighting profile that can be combined with multiple click diffusers (flat opal - 0022620, round opal - 0022621, square opal - 0022630) with a maximum LED strip width of 20mm. Can be mounted with 'Profile HO surface 16 raw alu.' or dedicated plates. Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



## PRODUCT OVERVIEW

Product name	Profile Shallow Wide Surface 30 CDE-9/T 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278025
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288226002

## DATA TABLE

### General data

Product name	Profile Shallow Wide Surface 30 CDE-9/T 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278025
Warranty	3 years

### Physical data

Housing colour	Silver
Nominal Product Length (mm)	2000
Nominal Product Width (mm)	33.4
Nominal Product Height (mm)	12.8
Weight (kg)	0.73

### Packaging

Single packaging type	Carton
Product EAN number	5410288226002
Packaging single length / height (cm)	200.0

## Profile Shallow Wide Surface 30

*Profile Shallow Wide Surface 30 CDE-9/T 2m anodised*

0022600

Packaging single width (cm)	3.0
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288226002
Units per outer package	50
Packaging outer length / height (cm)	205.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

### TECHNICAL DRAWINGS

