

**HSS hand reamer**  
for universal use up to 1000N/mm<sup>2</sup>



**Application**

For cutting H7 fit tolerances manually in through holes or with interrupted cutting conditions up to 1000 N/mm<sup>2</sup>.

**Version**

- 6° left-hand spiral, uneven pitch and long notch shape

**Advantage**

- Good bore hole quality (dimensional tolerance, roundness, surface quality)

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	●	●	○	○	○	●	○	●	○	●	○	○		○	○	○			

<b>Art. No.</b>	<b>11602 110</b>
<b>Cutting material</b>	HSS
<b>Tolerance of fit</b>	H7
<b>Groove type</b>	Left-hand twist, 6°
<b>Cutting edge diameter</b>	11 mm
<b>Length</b>	142 mm
<b>Cutting edge length</b>	71 mm
<b>Number of cutting edges</b>	8 PCS
<b>Shank square</b>	9 mm
<b>Form</b>	B

**EAN-Code**

4050293004632