

## Shelf boltless rack, single-row

Plastic-coated RAL 7035



### Application:


Universal shelving system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools

### Execution:

- Shelves height-adjustable in increments of 25 mm for variable adaptation to stored goods
- Shelves with a 50 mm hole grid to accommodate accessories, shelf edge height 40 mm
- For technical reasons, depth reinforcements are always zinc plated, even with coated frames
- Basic rack planning dimensions: Nominal length + 56 mm, nominal depth + 36 mm
- With dismantled or pre-assembled frame

### Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



|   |                  |
|---|------------------|
| <b>Art. no.</b>                         | <b>50167 044</b> |
| <b>Brand</b>                            | META             |
| <b>Manufacturer Part Number</b>         | 20097041         |
| <b>Height</b>                           | 2000 mm          |
| <b>Length</b>                           | 1056 mm          |
| <b>Depth</b>                            | 436 mm           |
| <b>Nominal length</b>                   | 1000 mm          |
| <b>Nominal depth</b>                    | 400 mm           |
| <b>Design</b>                           | Shelving unit    |
| <b>Type of assembly</b>                 | To insert        |
| <b>Surface</b>                          | Plastic-coated   |
| <b>Design of the frame</b>              | Disassembled     |
| <b>Grid dimension</b>                   | 25 mm            |
| <b>Number of shelves</b>                | 5 PCS            |
| <b>Load-carrying capacity per shelf</b> | 150 kg           |
| <b>Load-carrying capacity per field</b> | 1100 kg          |
| <b>Number of frame</b>                  | 2 PCS            |
| <b>Quality label</b>                    | RAL-RG 614/1     |
| <b>Made in</b>                          | Germany          |
| <b>Gross Weight</b>                     | 28.468 kg        |
| <b>Product Group</b>                    | 508              |

### EAN

4026212271812