

Manual forklift, manual hydraulic forklift truck

Carrying capacity 1000 kg

hanhart
CHRONOGRAPHEN 1882

Application:

Hand hydraulic stacker to lift and move palletised goods

Version:

- Stable welded, torsion-proof sectional steel structure
- Safe position even under full load
- Hydraulic lifting by means of drawbar or pedal
- Manual lowering infinitely adjustable via handle
- Safety draw bar with rubberised handle
- Hydraulic system with safety valve
- Hard chromium plated pressure piston
- With protective grating, fixed down to the bottom of the frame, against falling objects and for free sight to the front
- Quiet polyurethane rollers facilitate the work
- 2 large steering wheels with parking brakes, for optimum manoeuvring even in narrow spaces, ground clearance of fork arms 40 mm, allows bumps in the ground to be travelled over effortlessly, all forklift trucks comply both with the requirements of the regulations of the employers' liability insurance association of BGV-D27 and the Euronorm colour: RAL 5012, light blue, powder-coated



Art. no.	50262 500
Load-carrying capacity	1000 kg
Length	1705 mm
Width	755 mm
Fork length	1150 mm
Fork arm width	170 mm
Fork, external distance	550 mm
Fork roller diameter	83 mm
Min. lift height	90 mm
Lift height	1200 mm
Stroke height per pedal movement	20 mm
Castor-wheel diameter	150 mm
Material of steering wheels	Polyurethane
Min. overall height	1730 mm
Max. overall height	1750 mm
Colour	Light blue RAL 5012
Surface	Powder-coated
Turning radius	1400 mm
With free stroke	1085 mm
Travel drive	Manual
Fork castor design	Tandem

EAN-Code

4260151120590