

## Scissor-type lifting table carriages

Carrying capacity: up to 1500 kg

### Application:

Lift, lower and transport using just one device, for use as an adjustable serving trolley at assembly workplaces and as the ideal workshop and supply trolley with a wide range of commercial and industrial uses.

### Version:

- For loads from 150 kg up to 1500 kg, lifting heights from 225 mm to 1510 mm
- Stable scissor-type bracing
- Hand handle control, continuous height adjustment
- Lift operation via pedal
- Hydraulic pump made of high-strength steel
- 2 steering wheels with wheel block, 2 axis wheels
- Polyurethane wheels (PU) for low-noise and easy run
- Pressure relief valve for long life of the pump
- Colour: RAL 5012, light blue, powder-coated



<b>Art. no.</b>	<b>50262 910</b>
<b>Load-carrying capacity</b>	500 kg
<b>Min. table height</b>	340 mm
<b>Max. table height</b>	900 mm
<b>Stroke height per pedal movement</b>	15 mm
<b>Loading surface length</b>	855 mm
<b>Loading-surface width</b>	500 mm
<b>Loading surface thickness</b>	50 mm
<b>Shear design</b>	Single
<b>Colour</b>	Light blue RAL 5012
<b>Surface</b>	Powder-coated
<b>Number of steering rollers</b>	2 PCS
<b>Number of fixed rollers</b>	2 PCS
<b>Stroke mechanism</b>	Manual
<b>Lift height</b>	560 mm
<b>Length</b>	1165 mm
<b>Width</b>	500 mm
<b>Height</b>	970 mm

### EAN-Code

4260151120477