



## Halogen Lamps

### Operation lighting


For special features, specific benefits and areas of use see page 114



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter max. mm	Total length max. mm	Light centre length mm	Luminous flux lm	Average life h	Individual life h	Burning position	PU
8910002040	24V 40W axial silver cap	24	40	1.67		26	52	34	900	1,000			
8910002050	24V 50W axial silver cap	24	50	2.08		26	52	34	1,000	1,000			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter max. mm	Total length max. mm	Light centre length mm	Lumino- us flux lm	Average life h	Individual life h	Burning position	PU
00847805	22.8V 40W IRC	22.8	40		Special	12	51	36.5	1,200	800			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h	Burning position	PU
860002450K	Halogen lamp 24V 50W ceramic/flex	24	50		Special	12	240	36.5	850	600 bei 22.8V			