

**Cabtite (cable entry system)  
CABTITE GI X BK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The pluggable click inlays allow the frame openings to be configured as required for use with small or large sealing elements. An audible "click" confirms correct installation. This means that the Cabtite cable entry system can be variably configured for different requirements (cables, conductors, hoses, pneumatic and hydraulic lines).

**General ordering data**

Type	CABTITE GI X BK
Order No.	<a href="#">2584290000</a>
Version	grid inlay, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 17.5 mm, Width: 44 mm, Depth: 17.5 mm, -40 °C... 120 °C
GTIN (EAN)	4050118616439
Qty.	5 pc(s).

**Data sheet**

**Cabtite (cable entry system)  
CABTITE GI X BK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	44 mm	Length (inches)	1.732 inch
Width	44 mm	Width (inches)	1.732 inch
Height	17.5 mm	Height (inches)	0.689 inch
Height of lowest version	17.5 mm	Depth	17.5 mm
Depth (inches)	0.689 inch	Net weight	5.04 g

**General information**

UL 94 flammability rating	V-0	Halogen	No
Silicone	No	Sealing	TPE
Material	Polyamide, glass fibre-reinforced		

**Classifications**

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.0	27-18-28-15	eClass 9.1	27-18-92-65

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data	<a href="#">STEP</a> <a href="#">STEP</a>
User Documentation	<a href="#">Cabtite Installation Instructions</a>