

ABS 17/16-L3

PC1716_3
Sample image

Order symbol : ABS 17/16-L3

EAN : 6418074056764

Product nr : 7585105


El. number :

Description : Enclosure, ABS

- Finland :
- Denmark : 8212016758
- Sweden :

Remarks : Smoked transparent hinged cover

Including : Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices, FC version: Closed PC frame front plate with PUR gasket and cover screws.



Dimensions :	Height	Width	Depth
mm :	188	160	106
inch :	7.4	6.3	4.17

Materials :

Material : ABS

Accessories :

- FP 17/16 Front plate (aluminium), for enclosures: (160 x 100 x 0)
- MP 17/16 Mounting plate, for enclosures: (136 x 133 x 1)
- FC PC 17/16 Frame of PC front plate, for enclosures: (166 x 106 x 16)

Base colour :

Cover colour :

Gasket material : Polyurethane

Temperatures :

Temperature °C (short term) : -40 ... 80

Temperature °C (continuous) : -40 ... 60

Temperature °F (short term) : -40 ... 175

Temperature °F (continuous) : -40 ... 140

Rating :

Ingress protection (EN 60529): IP66; IP67;

Impact Resistance (EN 62262): IK07;

Electrical insulation : Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance : -

Flammability Rating : UL 94 HB

Glow Wire Test (IEC 695-2-1) °C : 650 °C

NEMA Class

Certificates :

SGSFIMKO_CARDpc