


### Assorted Chains

- outside use
- stainless steel



Sash-Chain



Ball-Chain



C-Link Chain



A-Link Chain



C-Link Chain



Calibrated Chain



Plastic Chain

Code No.	Description	d x t x b / mm	Reel-Type	m per Reel	working load limit kg **
<b>Sanitary Chains</b>					
T0120710117	● Sash-Chain, solid brass	0,3 x 10,5 x 4	A	50	-
T0120710127	● Sash-Chain, solid brass, nickel plated	0,3 x 10,5 x 4	A	50	-
T0120710217	● Sash-Chain, solid brass	0,4 x 12,5 x 5	A	50	-
T0120710227	● Sash-Chain, solid brass, nickel plated	0,4 x 12,5 x 5	A	50	-
T0120713017	● Sash-Chain, solid brass	0,5 x 19,5 x 7	A	25	-
T0120713027	● Sash-Chain, solid brass, nickel plated	0,5 x 19,5 x 7	A	25	-
T0120712617	● Ball-Chain, solid brass, nickel plated	2,5	A	100	-
T0120713627	● Ball-Chain, solid brass, nickel plated	3,6	A	25	-
T0120713617	● Ball-Chain, solid brass	4,5	A	25	-

#### Welded round link chains, form C long links, el. galvanized and blue chromed, DIN 5685

T0120332007	● C-Link Chain*	2,0 x 22 x 8	B	60	30
T0120333007	● C-Link Chain*	3,0 x 26 x 12	C	60	70
T0120334007	● C-Link Chain*	4,0 x 32 x 16	C	58	125
T0120335007	● C-Link Chain*	5,0 x 35 x 20	C	32	195
T0120336007	● C-Link Chain*	6,0 x 42 x 24	C	28	290
T0120337007	● C-Link Chain*	7,0 x 48 x 28	C	26	375
T0120338007	● C-Link Chain*	8,0 x 52 x 32	C	20	500

(\*also available in 30 m bundles)

#### Welded round link chains, form A short links, el. galvanized and blue chromed, DIN 5685

T0120313027	● A-Link Chain*	2,0 x 12 x 8	B	60	30
T0120313037	● A-Link Chain*	3,0 x 16 x 12	C	100	70
T0120313047	● A-Link Chain*	4,0 x 19 x 16	C	50	125
T0120313057	● A-Link Chain*	5,0 x 21 x 20	C	35	195
T0120313067	● A-Link Chain*	6,0 x 24 x 24	C	35	290
T0120313087	● A-Link Chain*	8,0 x 32 x 32	C	20	500
T0120313107	● A-Link Chain	10,0 x 40 x 37	C	10	630

(\*also available in 30 m bundles)

#### Welded round link chains, form C, stainless steel, Inox 316, DIN 5685

T0120192007	● C-Link Chain, Inox	2,0 x 22 x 8	B	30	30
T0120193007	● C-Link Chain, Inox	3,0 x 26 x 12	B	25	70
T0120194007	● C-Link Chain, Inox	4,0 x 32 x 16	B	20	125
T0120195007	● C-Link Chain, Inox	5,0 x 35 x 20	B	15	195

#### Calibrated round link chains, el. galvanized and blue chromed, DIN 766

T0120147665	● Calibrated Chain	5,0 x 18,5 x 17	C	40	250
-------------	--------------------	-----------------	---	----	-----

#### Plastic Chains, Polyethylene

T0120992007	● Plastic Chain, yellow/black	6,0 x 40 x 22	C	25	-
T0120993007	● Plastic Chain, red/white	6,0 x 40 x 22	C	25	-
T0120994007	● Plastic Chain, white	6,0 x 40 x 22	C	25	-
T0120995007	● Plastic Chain, black	6,0 x 40 x 22	C	25	-
T0120997007	● Plastic Chain, copper coloured	6,0 x 40 x 22	C	25	-
T0120991207	● Plastic Chain, yellow/black	8,0 x 48 x 26	C	25	-
T0120991807	● Plastic Chain, red/white	8,0 x 48 x 26	C	25	-
T0120998007	● Plastic Chain, black	10,0 x 61 x 33	C	12,5	-
T0120999007	● Plastic Chain, copper coloured	10,0 x 61 x 33	C	12,5	-
T0120991017*	● Plastic Chain, red/white	10,0 x 61 x 33	C	12,5	-

\*\* Specifications on the working load limit only for A and C formed chains

\* Discontinued, while quantity lasts