






INCANDESCENT LAMP, TRANSPARENT, RATED VOLTAGE AC/DC 60V, 1.0 W, WEDGE BASE W2 X 4.6D WEDGE-BASE W2 X 4.6D RATED VOLTAGE AC/DC 60V TRANSPARENT

Figure similar

General technical data:		
<b>Product designation</b>		incandescent lamp
<b>Type of light source</b>		filament lamp
<b>Color of the light source</b>		clear
<b>Mounting type</b>		W2 x 4.6d
<b>Product component</b>		
• series resistor		No
• diode		No
• lamp transformer		No
• Light source		Yes
<b>Type of voltage for actuation</b>		AC/DC
<b>Operating voltage</b>		
• with AC		
— at 50 Hz Rated value	V	60 ... 60
— at 60 Hz Rated value	V	60 ... 60
• for DC Rated value	V	60 ... 60
<b>Consumed current for rated value of supply voltage maximum</b>	mA	25
<b>Type of electrical connection</b>		Miscellaneous
<b>Mounting type</b>		miscellaneous

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other		
 UL		 EG-Konf.	<a href="#">Special Test Certificate</a>	<a href="#">Environmental Confirmations</a>	<a href="#">other</a>

<b>other</b>
<a href="#">Confirmation</a>

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB29081AF>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3SB29081AF/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3SB29081AF&lang=en>

last modified:

09.03.2015