

USB interface for PRO Devices. Pre-wired cable and connector, USB2.0 Typ A. IP65 degree of protection with closed protective cap. Will be integrated in basic adapter via side cover

General information

Product type designation USB interface for PRO devices

Control elements

Connection type

- USB Yes; USB 2.0 type A
- Cable length 0.5 m

Installation type/mounting

Mounting Integrated by means of cover on the side of the basic adapter.

EMC

Emission of radio interference acc. to EN 55 011

- Limit class A, for use in industrial areas Yes

Degree and class of protection

IP65 (all-round) Yes; IP65 fully enclosed (when protective cover is closed)

IP (at the front) IP20 when protective cover is open

Standards, approvals, certificates

CE mark Yes

Ambient conditions

Ambient temperature during operation

- min. 0 °C
- max. 50 °C

Ambient temperature during storage/transportation

- min. -20 °C
- max. 60 °C

Air pressure acc. to IEC 60068-2-13

- Installation altitude above sea level, max. 3 500 m

Relative humidity

- Operation, max. 90 %
- Condensation permissible No

Cables

Cable length 0.5 m

Mechanics/material

Material Brass, nickel-plated

Enclosure material (front)	USB cover: Anodized aluminum, cover for basic adapter: Aluminum, powder-coated, RAL 9006
Enclosure color (front)	Silver-metallic
Service life	
• Number of operating cycles, keys	1 500; Insertion cycles
Dimensions	
Enclosure diameter	22.5 mm; Hole diameter in the cover for the basic adapter
Overall depth	20 mm
Weights	
Weight without packaging	0.25 kg
Weight incl. packaging	0.53 g
Scope of supply	
Delivery quantity in pieces	1
Components included	USB socket with cable and connector, cover for the basic adapter, bolts for fastening
Other	
Usable in the following products	
• Product 1	6AV7674-1KA00-0AA0
last modified:	10/13/2017