


# CLIFF

## GOLD JACK SOCKETS


### 6.35mm JACK SOCKET




**CL11607**





**SCHMATIC**




**CL12207**



**CL12327**



**CL12345**



**SPECIFICATION**

Withstand voltage:	2000V DC Min.
Maximum Current:	5A
Temperature Rating:	-10° C to +70° C
Life (Minimum):	10,000+ Operations
Nominal Contact Resistance:	<50mΩ

**DESCRIPTION**

- CL11607** - Jack Socket Mono S2/BNB Solder Tag
- CL12207** - Jack Socket Stereo S2/BBB Solder Tag
- CL12327** - Jack Socket Stereo S2/BBB PC Tag Type A.
- CL12345** - Jack Socket Stereo S2/BBB Special Nose PC Tag Type C. No nut or washers.




# CLIFF

## GOLD JACK SOCKETS



### 6.35mm JACK SOCKET





**CL13345**



**CL1308G**



**CL13106G**



### DESCRIPTION

- CL13345** - Jack Socket Stereo S4/BBB PC tag type C
- CL1308G** - Jack Socket Mono S4/BNB PC tag type A
- CL13106G** - Jack Socket Mono S4/BNB PC tag type C





### 3.5mm JACK SOCKET



**CL13845G**



**CL13843G**



### DESCRIPTION

- CL13845G** - 3.5mm Jack Socket S6G/BB with nut
- CL13843G** - 3.5mm Jack Socket S6G/BB without nut

# CLIFF

## GOLD JACK SOCKETS

### 3.5mm JACK SOCKET









#### FCR1295G

##### SPECIFICATIONS

- WITHSTAND VOLTAGE: 2000V DC min
- MAXIMUM CURRENT: 5A
- TEMPERATURE RANGE: -10°C TO +70°C
- LIFE (MINIMUM): 5,000+ OPERATIONS
- CONTACT RESISTANCE <math>< 50\text{m}\Omega</math>

##### DESCRIPTION

**CL1295G** - 3.5mm Stereo Jack Socket S9/BBB with 6mm PCB legs



### JACK SOCKET ACCESSORIES



**FCR14422** - EMI / RFI SCREEN FOR 6.35mm JACK SOCKETS



**CL14218** - BLACK COMBINED NUT/BEZEL FOR S4 TYPE JACK SOCKET



**CL14218GY** - GREY COMBINED NUT/BEZEL FOR S4 TYPE JACK SOCKET

**CL1396** - RECESS PLATE TO ALLOW FLUSH MOUNTING OF 6.35mm JACK SOCKETS

