

STM 550U Multisensor Module

STM 550U enables the realization of energy harvesting wireless sensors communicating according to EnOcean Alliance radio standard. Key applications are wall-mounted or equipment-mounted sensor solutions for the measurement of temperature, humidity, illumination or acceleration / orientation.

STM 550U integrates dedicated sensors for temperature, humidity, illumination, acceleration and magnet contact. These sensors measure and transmit the current status every 60 seconds.

STM 550U will immediately wake-up and transmit an update if an acceleration event occurs (e.g. due to being moved or shaken) after a period without such change.

STM 550U contains an integrated solar cell optimized to generate the required energy based on available ambient lighting. Under typical indoor lighting scenarios (200 lux for 6 hours per day) they operate fully self-supplied. For use cases with insufficient available light, it is possible to mount a dedicated backup battery.



STM 550U provides an integrated NFC interface that can be used for device configuration and device commissioning and an LRN button that can be used for simple commissioning tasks.

STM 550U is delivered as module in PTM 21x form factor for integration into OEM customer designs.

Alternatively, EMSIU is available as white label product (WLP) in single unit packaging containing module, wall mount, front cover, magnet and adhesive tape while STM 550U KIT provides module, wall mount, front cover, magnet and adhesive tape in one box for volume deliveries.

Order information

Type	Frequency	Variant	Order Code
STM 550U	902.875 MHz	Module	S6251-K516
EMSIU		WLP	E6251-K516
STM 550U KIT		Kit	B6251-K516

Features overview

Transmission Frequency / Data Rate	902.875 MHz / 125 kbps
Transmission Power	+99 dBμV
Transmission Range (for guidance only)	typ. 200 m free field / 30 m indoor environment
Temperature Measurement Range / Accuracy	-20 °C ... +60 °C (NOTE 1) / ± 0.3 K
Humidity Measurement Range / Accuracy	0 ... 100 % r.h. (NOTE 1) / ± 3% r.h.
Illumination Measurement Range / Accuracy	0 ... 65000 Lux (NOTE 1) / ± 10 %
Acceleration Measurement Range / Accuracy	± 2 g / ± 0.03 g
Acceleration Wake Threshold	0.03 g (default, configurable via NFC)
Update Rate (excl. random offset)	Every 60 seconds (configurable via NFC)
Device Configuration	NFC (ISO 14443)
Supported EEP (selectable via NFC)	D2-14-41 (default) D2-14-40, A5-02-05, A5-04-01, A5-04-03 A5-06-02, A5-06-03, A5-14-05, D5-00-01
Power Supply	Integrated solar cell
Operating Time In Darkness (at 25°C)	4 days (after full charge)
Backup Power Supply (optional)	CR1632
Dimensions (STM 550U module)	40 mm x 40 mm x 13 mm
Operating Temperature / Humidity	-5°C ... +45°C / 0 ... 90% r.h. (non-condensing)

Note 1: Sensor measurement range is dependent on the selected EEP

STM 550U should only be used in the operating conditions (temperature / humidity) specified above