

Han-Yellock 30 cover for hood



Part number	11 12 300 5451
Specification	Han-Yellock 30 cover for hood
HARTING eCatalogue	https://b2b.harting.com/11123005451

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han-Yellock [®]
Type of accessory	Protection cover
Description of the accessory	for carrier hoods With fixing cord Thermoplastic

Version

Size Han-Yellock [®] 30	
----------------------------------	--

Technical characteristics

Limiting temperature	-40 +125 °C
Un-/locking temperature	-10 +85 °C
Degree of protection acc. to IEC 60529	IP65
	IP67

Material properties

Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Material properties

California Proposition 65 substances California Proposition 65 substances Lead Nickel Fire protection on railway vehicles EN 45545-2 (2020-08) Requirement set with Hazard Levels Requirement set with Hazard Levels	REACH SVHC substances	Not contained
Fire protection on railway vehicles EN 45545-2 (2020-08) R22 (HI 1-3)	California Proposition 65 substances	Yes
R22 (HL 1-3)	California Proposition 65 substances	
Requirement set with Hazard Levels	Fire protection on railway vehicles	EN 45545-2 (2020-08)
R23 (HL 1-3)	Requirement set with Hazard Levels	

Specifications and approvals

Specifications	IEC 60664-1
Specifications	IEC 61984

Commercial data

Packaging size	1
Net weight	30 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110151
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors