

Bez.: UHF-Aufdrehstecker, mit Kabelöffnung für max. 10,0 mm, RG 8(A) - 213/U, Teflon-Isolation

Impedance	Non-constant
Frequency range	0 ~ 300 MHz
Voltage rating	500 Volts peak
Dielectric Withstanding Voltage	1500 VRMS min
Insulator Resistance	5000 M Ω min.
Contact Resistance	Center Contact: 3 m Ω max. Outer Contact: 2 m Ω max.
Temperature range	-65°C ~ +165°C

NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BODY/CONTACT: BRASS PER JIS-C3604
2. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL 70 μ MIN THICK OVER COPPER STRIKE
6. GOLD PL 1-3 μ OVER NICKEL PL 70 μ MIN THICK OVER COPPER STRIKE

4	Shell	Brass	Nickel
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
No	Description	Material	Finish

