

# KERN FK250

Robust Push/Pull force gauge for simple measurement



## Services (optional)

DAkkS Calibration certificate (Pressure):	963-2610
DAkkS Calibration certificate (Tensile):	963-1610
DAkkS Calibration certificate (Tensile/Pressure):	963-3610
Factory calibration certificate (Pressure):	961-2610
Factory calibration certificate (Tensile):	961-1610
Factory calibration certificate (Tensile/Pressure):	961-3610

## Category

Brand:	Sauter
Category:	Force gauges
Product Group:	Electronic force-measuring device

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	248 x 230 x 80 mm
Gross weight:	887 g
Net weight:	600 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	195 x 82 x 35 mm
Overall dimensions mounted (WxDxH):	195 x 82 x 35 mm

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Measuring capacity [Max]:	250 N
Overload protection (of [Max]):	200 %
Precision (of [Max]):	0,500 %
Preset unit:	N
Readability [d]:	0,100 N
Test frequency:	1000 Hz

## Display

Display digit height (large):	1,800 cm
-------------------------------	----------

## Functions

Data hold function:	yes
Display revolving:	yes
Peak function:	yes

## Environmental conditions

Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

## Power supply

Battery:	6x1.5 V AA
Input voltage:	100 V - 240 V
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH US UK
Operating time:	25 h