

datasheet for KLEPS 250
 article number: 973528100



product description:	order number: 973 528-100
description:	Contact-protected clamp-type test probe with rotating grip jaws and flexible shaft. The grip jaws allows clamping of pins and wires up to a max. of 4 mm diameter. Brass 4 mm diameter contact-protected socket connection. Connects with MLN and MLB measuring leads.
typ:	KLEPS 250 schwarz/black
system:	4mm sliding sleeve system
order number:	973 528-100
clamping range:	4 mm
clamping typ:	rotating grip jaws
color	●
other color versions:	● ●
technical data	
measurement category acc. to IEC 61010:	CAT I
norm	IEC 61010
type of termination:	4 mm socket (unsprung)
rated voltage:	30 VAC / 60 VDC
rated current:	4 A
Please consider derating curve!	
contact resistance:	100 mOhm
material	
contact material:	grip jaws: spring steel socket: brass
contact surface material:	grip jaws: tin
housing material:	PF
environmental conditions:	
temperature range:	-25 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 V - 0
drawing	

