

Temperature Controlled Soldering Stations

- The temperature range can be controlled between 200°C and 450°C. The WHS40 soldering station from Weller rules out the risk of temperature shocks which can occur with conventional soldering bits.
- Desired temperatures can be set precisely in such a way that you no longer have to worry about overheating sensitive areas.
- Consist of power unit, soldering iron with nickel-plated tip 2,0 mm and safety rest.



Type	Code No.	Watts	Volts	Hz	Weight g	Shelf Pack
WHS40	T0056806699N	40	230	50	1460	1
WHS40 (UK)	T0056806399N	40	230	50	1488	1

Temperature Controlled Digital Soldering Stations

- The new electronically controlled soldering station WHS40D operates with a temperature range of 150°C–450°C.
- The precise soldering tip temperature shows on the digital read-out (pre-set and real value).
- This soldering station is suitable for delicate soldering tasks on temperature sensitive components.
- LED to monitor the heater is integrated in the display.
- The temperature adjusts via buttons.
- Consist of power unit, soldering iron with “Longlife” tip 2,0 mm and safety rest.



Type	Code No.	Watts	Volts	Hz	Weight g	Shelf Pack
WHS40D	T0056828699N	40	230	50	1460	1
WHS40D (UK)	T0056828399N	40	230	50	1490	1

Straight Tips for Soldering Stations WHS40 and WHS40D

Type	Code No.	Packed	Nickel plated	Longlife	Diameter mm	Width mm	Shelf Pack
43113	T0054311399	Polybag	x		3,5	2,0	1
S3	T0054003499	Carded	x		3,5	3,5	6
S31	T0054321099	Carded		x	3,5	0,4	6
S32	T0054321199	Carded		x	3,5	2,0	6

(S3 = 3 tips on card)

Spare Parts for Soldering Stations WHS40 and WHS40D

Type	Code No.	Description	Weight g	Shelf Pack
WH40	T0056810699N	Soldering Iron with “Longlife” tip 2,0 mm	116	1
	T0058743708	Sponge (2 pcs.)	5	1
	T0058743709	Spring with funnel	35	1

Soldering Tips, Nickel-Plated, Packed in Polybag

For Soldering Iron	Type	Code No.	Description	Diameter mm	Width mm	Shelf Pack
SP15L / SI15 / SP15N	43113	T0054311399	straight	3,5	2,0	6
	43115	T0054311599	straight	3,5	3,5	6
SI25	43003	T0054300329	straight	4,5	4,5	6
	43004	T0054300499	bent	4,5	4,5	6
SP40L / SI40 / SP40N	43105	T0054310500	straight	6,3	6,3	6
	43108	T0054310899	bent	6,3	6,3	6
SP80L / SI75 / SP80N	43106	T0054310629	straight	9,5	9,5	6
	43109	T0054310929	bent	9,5	9,5	6
SI100 / SI120	43107	T0054310799	straight	12,5	12,5	6
	43110	T0054311000	bent	12,5	12,5	6
SI175	43111	T0054311199	bent	16,0	16,0	6
SI251	43112	T0054311299	bent	20,0	20,0	6

Soldering Tips, Iron-Plated "Longlife", Packed on Card

For Soldering Iron	Type	Code No.	Description	Diameter mm	Width mm	Shelf Pack
SP15L / SI15 / SP15N	S31	T0054321099	straight	3,5	0,4	6
	S32	T0054321199	straight	3,5	2,0	6
SI25	S33	T0054320099	straight	4,5	2,0	6
	S34	T0054320199	straight	4,5	3,0	6
	S35	T0054320299	straight	4,5	5,0	6
SP40L / SI40 / SP40N	S36	T0054322099	straight	6,3	5,0	6
	S37	T0054322299	bent	6,3	5,0	6
SP80L / SI75 / SP80N	S38	T0054323099	straight	9,5	7,0	6
	S39	T0054323299	bent	9,5	7,0	6
	MTG20	T0054313799	straight	9,5	9,5	6
SI100 / SI120	S41	T0054324399	bent	12,5	12,5	6

Replacement Parts for Soldering Irons

For Soldering Iron	Type	Code No.	Description	Shelf Pack
SI120	64256	T0056425699	Replacement heating element	1
SI175	64266	T0056426699	Replacement heating element	1
SI251	64276	T0056427699	Replacement heating element	1