



Gerade Aufschraub-Verschraubungen
Innengewinde: Whitworth-Rohrgewinde - Zylindrisch

Female Stud Couplings
Female Thread: BSP - Parallel

Reihe Series	Druck Pressure PN	Rohr A.D. Tube O.D. D1	Gewinde Thread G	Ca. Maße Approx. Dimensions					Bestellzeichen Order-Code Standard	Brutto-Preis Gross-Price Euro (€)
				L1	L2	i	SW1	SW3		
L	315	6	G 1/8"	36,0	19,0	12,0	14	14	GAI-L-06-G 1/8"	12,02
L	315	6	G 1/4"	41,0	24,0	17,0	19	14	GAI-L-06-G 1/4"	14,06
L	315	6	G 3/8"	42,0	24,0	17,0	24	14	GAI-L-06-G 3/8"	18,12
L	315	6	G 1/2"	46,0	31,0	20,0	27	14	GAI-L-06-G 1/2"	22,70
L	315	8	G 1/8"	36,0	19,0	12,0	14	17	GAI-L-08-G 1/8"	16,20
L	315	8	G 1/4"	41,0	24,0	17,0	19	17	GAI-L-08-G 1/4"	15,85
L	315	8	G 3/8"	42,0	25,0	17,0	24	17	GAI-L-08-G 3/8"	18,12
L	315	8	G 1/2"	46,0	32,0	20,0	27	17	GAI-L-08-G 1/2"	23,19
L	315	10	G 1/8"	36,0	19,0	12,0	17	19	GAI-L-10-G 1/8"	16,25
L	315	10	G 1/4"	42,0	25,0	17,0	19	19	GAI-L-10-G 1/4"	15,80
L	315	10	G 3/8"	43,0	26,0	17,0	24	19	GAI-L-10-G 3/8"	19,17
L	315	10	G 1/2"	47,0	30,0	20,0	27	19	GAI-L-10-G 1/2"	23,75
L	315	12	G 1/4"	42,0	25,0	17,0	19	22	GAI-L-12-G 1/4"	18,66
L	315	12	G 3/8"	43,0	26,0	17,0	24	22	GAI-L-12-G 3/8"	18,66
L	315	12	G 1/2"	48,0	30,0	20,0	27	22	GAI-L-12-G 1/2"	21,70
L	315	15	G 3/8"	46,0	27,0	17,5	24	27	GAI-L-15-G 3/8"	21,99
L	315	15	G 1/2"	49,0	31,0	20,0	27	27	GAI-L-15-G 1/2"	24,90
L	160	15	G 3/4"	53,0	34,0	22,0	32	27	GAI-L-15-G 3/4"	43,13
L	315	18	G 3/8"	47,0	26,5	17,5	27	32	GAI-L-18-G 3/8"	29,83
L	315	18	G 1/2"	50,5	30,5	20,0	27	32	GAI-L-18-G 1/2"	29,83
L	160	18	G 3/4"	53,5	33,5	22,0	36	32	GAI-L-18-G 3/4"	43,13
L	160	22	G 1/2"	55,0	33,5	20,0	32	36	GAI-L-22-G 1/2"	40,21
L	160	22	G 3/4"	56,0	35,5	22,0	36	36	GAI-L-22-G 3/4"	38,40
L	160	28	G 3/4"	57,5	35,0	22,0	41	41	GAI-L-28-G 3/4"	69,20
L	160	28	G 1"	60,5	38,0	24,5	41	41	GAI-L-28-G 1"	54,15
L	160	35	G 1 1/4"	68,5	41,0	26,5	55	50	GAI-L-35-G 1 1/4"	89,48
L	160	42	G 1 1/2"	69,5	42,5	28,5	60	60	GAI-L-42-G 1 1/2"	112,49

Reihe Series	Druck Pressure PN	Rohr A.D. Tube O.D. D1	Gewinde Thread G	Ca. Maße Approx. Dimensions					Bestellzeichen Order-Code Standard	Brutto-Preis Gross-Price Euro (€)
				L1	L2	i	SW1	SW3		
S	630	6	G 1/4"	42,0	26,0	17,0	19	17	GAI-S-06-G 1/4"	15,93
S	630	6	G 3/8"			17,0	24	17	GAI-S-06-G 3/8"	*
S	630	6	G 1/2"	48,0	31,0	20,0	27	17	GAI-S-06-G 1/2"	*
S	630	8	G 1/4"	43,0	26,0	17,0	19	19	GAI-S-08-G 1/4"	16,31
S	630	8	G 3/8"	44,0	27,0	17,0	24	19	GAI-S-08-G 3/8"	21,80
S	630	8	G 1/2"	48,0	31,0	20,0	27	19	GAI-S-08-G 1/2"	23,70
S	630	10	G 3/8"	45,0	26,5	17,0	24	22	GAI-S-10-G 3/8"	21,47
S	630	10	G 1/2"	49,5	30,5	20,0	27	22	GAI-S-10-G 1/2"	23,52
S	630	12	G 1/4"	46,0	27,5	17,0	22	24	GAI-S-12-G 1/4"	23,01
S	630	12	G 3/8"	45,0	26,5	17,0	24	24	GAI-S-12-G 3/8"	22,37
S	630	12	G 1/2"	50,0	30,5	20,0	27	24	GAI-S-12-G 1/2"	23,52
S	630	14	G 3/8"	50,0	30,0	17,0	24	27	GAI-S-14-G 3/8"	29,90
S	630	14	G 1/2"	52,0	32,0	20,0	27	27	GAI-S-14-G 1/2"	28,12
S	400	16	G 3/8"	48,0	26,5	17,5	27	30	GAI-S-16-G 3/8"	29,81
S	400	16	G 1/2"	53,0	31,5	20,0	27	30	GAI-S-16-G 1/2"	29,81
S	400	16	G 3/4"	55,0	34,5	22,0	36	30	GAI-S-16-G 3/4"	42,72
S	400	20	G 1/2"	57,0	32,5	20,0	32	36	GAI-S-20-G 1/2"	39,34
S	400	20	G 3/4"	60,0	34,5	22,0	32	36	GAI-S-20-G 3/4"	43,13
S	400	25	G 3/4"	60,0	35,0	22,0	41	46	GAI-S-25-G 3/4"	60,03
S	400	25	G 1"	66,5	37,5	24,5	41	46	GAI-S-25-G 1"	60,03
S	400	30	G 1 1/4"	72,5	42,0	26,5	55	50	GAI-S-30-G 1 1/4"	104,82
S	315	38	G 1 1/2"	79,5	43,5	28,5	60	60	GAI-S-38-G 1 1/2"	127,82