


EBC001



Splitter box

ZDO4H050MSS0000-00STAK120MSS



Application

Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes

Electrical data


Operating voltage	[V]	< 30 AC/DC; ("supply class 2" to cULus)
Max. current load per module/slot	[A]	4
Max. current load total	[A]	12

EBC001



Splitter box

ZDO4H050MSS0000-00STAK120MSS

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 67; ("enclosure type 1" according to cULus)
Mechanical data	
Weight [g]	236.5
Dimensions [mm]	33 x 60 x 118.2
Materials	PA
Number of ports splitter box	4
Connector type	M12
Accessories	
Accessories (supplied)	Protective caps: 2 labels: 4
Remarks	
Pack quantity	1 pcs.
Electrical connection - Connection	
Connector: 1 x M23; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm	
	


EBC001



Splitter box

ZDO4H050MSS0000-00STAK120MSS

Connection



Electrical connection - slot

Connector: 4 x M12; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

