


CAP FOR D-BOX M12 6-WAY 5-POLE

Pot.-sep. 10m PUR/PVC-JB, 12x0,34+5x0,75

for 6-way distribution boxes, 5-pole
PUR/PVC
10.0 m
potentially separated
New Art.-No. 8000-86659-3921000

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals



Technical Data

Total current max. 2 × 8 A

Cables

No./diameter of wires 12×0.34 + 5×0.75 mm²

C-track properties 2 Mio.

Material (jacket) PUR/PVC

Outer diameter approx. 11.5 mm

Bend radius (moving) 12 × outer Ø

Cable number 392

General data

Dimensions H × W × D 33×48×68 mm

Commercial data

country of origin CZ

customs tariff number 85444290

minimum order quantity 1