



EXHAUST FILTERS MOUNTING CUT OUT 177X177
MM RAL 7035 DEGREE OF PROTECTION IP 54
ACCURACY CLASS 3

Figure similar

Model		
product brand name		SIVACON
Product designation		outlet filter
Type of ventilation		ventilation
Fan design / Insertable fan		No
Design of the product / EMC version		No
General technical data		
Cutout width	mm	177
Cutout height	mm	177
Operating temperature / minimum	°C	-20
Protection class		
Protection class IP		IP54
Appearance		
Color		RAL 7035
Product details		
Product component / Fan		No
Mechanical Design		
Height	mm	204
Width	mm	204
Depth	mm	32
Installation location		Control cabinet...panels, door
Mounting type		snap-on mounting
Mounting type		

- 19-inch installation
- wall mounting

No
Yes
plastic

Material

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

V
V

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR64005GV30>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR64005GV30/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR64005GV30

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015