

Accessory

PICO-LPG-405-532
Order Number: 70140316

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-50		85	°C
Storage Temperature	-50		80	°C

Technical Parameters

RoHS yes

Optical Parameters

Luminous transmittance	48.00 %
LB Rating	180-315 D LB7 + IR LB4, >315-532 DIRM LB6
Lens Color	Orange

Mechanical Parameters

Size	144x145x50 mm
Material	Polymer
Housing Color	black
Weight	10 g

(*) Over the complete operating temperature range

Features



- Complete protection
- Comfortable fit over prescription glasses or alone
- Adjustable temples and side-shields for wide field of view
- CE Certified EN 207
- With Picotronic Logo imprint

Picture



Safety Label



Valid Revision

| 12-FEB-2021