



Art No. CH0011

Cable HDMI 1.3b HQ 2x male 2 meter

ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE

HDMI MALE PLASTIC:BLACK

DETAIL P1

HDMI MALE PLASTIC:BLACK

DETAIL P2

2000±30

LogiLink
LOGO:BLUE(INK-8XX)

TO-0127

BACK SIDE

CKT 18

TO-0127

BACK SIDE

CKT 18

NOTE:

1.CABLE: UL-20276 [30AWG(7/0.103)*P INS:F0-SKIN + DW(7/0.103) + AL/MY(SPREAD THE WRING)*4.C + 30AWG(7/0.103)*P INS:HD-PE + 30AWG(7/0.103)*5C INS:HD-PE + AL/MY + B.D(85%)T.C PVC JACKET 0D:6.0±0.2mm COLOR:MATT BLACK(INK-K01).

2.CONNECTOR:
P1 & P2: HDMI 19P MALE IDC TYPE CONTACT:15U"; SHELL:GOLD-PLATED,(TWO-COLOR MOLD)

3.P1&P2 SHIELD:COPPER FOIL 360° SOLDER TO CONNECTOR SHELL & CABLE BRAID.

4.HOOD:P1&P2:MOLDED TYPE,PVC 45P,COLOR:BLACK(INK-K01).

5.ELECTRICAL TEST:
(1)100% OPEN SHORT & MIS WIRE TEST.
(2)CONTACT RESISTANCE 3 ohm Max.
(3)INSULATION RESISTANCE 10M ohm Min.
(4)HI-POT DC300V/0.01SEC.
6.PACKING: SEE P-0210 PACKING DRAWING

Tolerance	Inch	MM	Title
X	.015	.30	HDMI/M - HDMI/M CABLE
XX	.010	.10	
XXX	.005	.05	
Drawn: ZMMIS 09/12/07			
Check:		Customer P/N: CH0011	Customer: E-DIR
App'd:		Scale: NONE	Unit: 1/8" = 1/4" Projection
Eng'r:		Dwg No. 200-0855	Sheet 1/2