

**FEX FEX 1919 13 T**



Sample photo

**Order symbol:** FEX 1919 13 T  
**Product nbr:** 4120800  
**Description:** Enclosure, PC  
**Remarks:** Ex e II, EN 60079; IK 4J

**EAN:** 6418074007865  
**EI. number:**  
 Finland: 3424636  
 Electric No. Denmark: 8212026311  
 Electric No. Italy: 7801010  
 Electric No. Sweden: 4120800

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions:			Accessories:	
Length	Width	Height		
mm:	188	188	130	EKJVT Mounting plate
inch:	7.4	7.4	5.1	EKMVT Mounting plate
Materials:			EKOVT Mounting plate	EKPVT Mounting plate
<b>Material:</b>	Polycarbonate		EKTVT Mounting plate	EKUVT Mounting plate
<b>Base colour:</b>	RAL 7035 -light grey		EKV 12 DIN-35 Mounting rail	EKV 22 DIN-35 Mounting rail
<b>Cover screws material:</b>	Polyamide		EKV 32 DIN-35 Mounting rail	
<b>Cover colour:</b>	Clear transparent		Rating:	
<b>Cover screws colour:</b>	Grey		Ingress Protection (EN 60529): IP54	
<b>Gasket material:</b>	Silicone		Electrical insulation: Totally insulated	
Temperatures:			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperature °C (short term):</b>	-40 ... 120 °C		Impact Resistance (EN 50014): 4J	
<b>Temperature °C (continuous):</b>	-10 ... 80 °C		Certificates:	
<b>Temperature °F (short term):</b>	-40 ... 250 °F		ATEX	
<b>Temperature °F (continuous):</b>	14 ... 175 °F		Attestation of Conformity	
Accessories:				
EKHVT	Mounting plate			

