

NSYCRS25W240V

Climasys Ultra thin resistance heater low starting current 20W 240V 130x250mm



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Power range	25 W
Input voltage	240 V AC 50/60 Hz
Electrical connection	Cable 6.56 ft (2 m)

Complementary

Operating position	Vertical Horizontal
Ambient air temperature for operation	-76...158 °F (-60...70 °C)
Temperature setting range	-40...158 °F (-40...70 °C)
Material	Silicone rubber
Height	External 4.33 in (110 mm)
Width	External 9.06 in (230 mm)
Depth	External 0.06 in (1.6 mm)
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories
Condition of use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
Fixing mode	By 4 screws
Mounting support	Standard mounting plate DIN rail Adhesive Velcro Telequick mounting plate

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	00785901806714
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.77 in (4.5 cm)
Package 1 width	10.24 in (26 cm)
Package 1 Length	11.02 in (28 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------