

Product data sheet

Item No. 92.207.1003.1

Cable assembly GST18I4KSB- 15 10SW

geis® Connection cable female - free end; length: 1m; type GST18I4; 4-pole; 250/400 V / 16 A; colour of coding: black with black strain-relief; cable: H05VV-F 4G1,5, colour: black



Item No.	92.207.1003.1
EAN	4015573597747
Order Unit	50 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	4
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	35 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05VV-F

Cable colour	Black
Cable diameter	9.2 mm
Version of cable	Female - free end
Type of cord set	Connection cable
Version cable end 1	GST18i4 socket
Version cable end 2	Free end

Material

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	1 m
--------------	-----

Technical drawing

Pol / Aderfarbe / pole colour of core

L2	schwarz / black
N	blau / blue
⊕	grün-gelb / green-yellow
L1	braun / brown

.F / Farbe / colour

1	schwarz / black	2 N PE 1	schwarz / black
2	weiß / white	⊕	weiß / white
3	grau / grey	2 N PE 1	schwarz / black

Teilenummern / Part numbers

Teil-Nr. / part-no.	L	Beispiel (Farbe: schwarz) / example (colour: black)	Typ / type
92.207.XX03.F	XX in dm-Schritten	92.207.1003.1 = 10dm/L= 1000mm	GST18i4KSB- 15 10SW
U2.207.XX03.F	XX in m-Schritten	U2.207.1203.1 = 12 m/L=12000mm	GST18i4KSB- 15 X10SW

Weitere Daten siehe Katalog / further data see catalog

Typ/type: GST18i4KSB- 15

SW = schwarz/black
WS = weiß/white
GR01 = grau/grey

PRE-ASSEMBLED CABLE KONFEKT_LEITUNG

Buchse/female = Treies Ende/free end 1,5mm
Schraubanschluss/screw connection 2,5mm