

Conical countersink, 90°, HSSE-TiN, triple cutter
for universal use up to 1000 N/mm²

ORION®

Application:

For producing 90° counterbores up to 1000 N/mm².

Execution:

- profile-ground triple-edge countersink with radial relief

Advantage:

- radial relief ensures optimum chip breaking



Art. no.	11501 196
Brand	ORION
Manufacturer Part Number	11501196
Countersink angle	90 Degree
Cutting material	HSS
Surface	TiN
Number of cutting edges	3 PCS
Tool holding device	HA parallel shank
Spot-facer diameter	16.5 mm
Tip diameter	3.2 mm
Shank diameter	10 mm
Length	60 mm
f steel 700	0.14 mm/r
DIN	335
Gross Weight	0.041 kg
Product Group	1EH

EAN

4053625032624