

Workplace mats made of PVC, manufactured to request

Textured structure, height 12.7 mm



Application:


For average durability in dry areas.

Execution:

- Microcellular vinyl with Dyna-Shield™ layer, non-slip surface R10 according to DIN 51130 and BG Rule BGR181
- Fire protection class 2 according to NFPA 101
- Mats delivered with four bevelled edges
- Weight: 4 kg per m²
- Available upon request: Surface with wide transverse or longitudinal grooves, in bulb plate look

Advantage:

- Excellent standing comfort and increased durability thanks to Dyna-Shield™ surface - 50% more compared to conventional microcell vinyl floor covering



Art. no.	50225 621
Brand	NOTRAX
Manufacturer Part Number	417C0036GY
Surface structure	Burling / closed
Material	PVC - Polyvinyl chloride
Width	910 mm
Material thickness	12.7 mm
Mat design	Bulk stock
Min. temperature resistance	-10 °C
Max. temperature resistance	70 °C
Suitable for wet areas	No
Antistatic	No
Anti-fatigue	Yes
Non-slip	Yes
Compliant with REACH	Yes
Colour	Grey
Gross Weight	3.500 kg
Product Group	5AD

EAN

0662641740976