



Appliance Oven Tubular

Appliance 25W E14 230-240V T25 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

Product data

• General Characteristics

| | |
|------------------------|----------------------------|
| Cap-Base | E14 |
| Bulb | T25 [T 25mm] |
| Bulb Finish | Clear |
| Operating Position | any [Any or Universal (U)] |
| Main Application | Oven |
| Nominal Lifetime | 1000 hr |
| Rated Lifetime (hours) | 1000 hr |
| Rated Lifetime (years) | 1 an |

• Light Technical Characteristics

| | |
|-----------------------|---------|
| Color Rendering Index | 100 Ra8 |
| Color Temperature | 2700 K |
| Luminous flux lamp | 172 Lm |
| Rated Luminous Flux | 172 Lm |

• Electrical Characteristics

| | |
|--------------------------------|--------------------|
| Rated Wattage | 25.0 W |
| Lamp Wattage | 25 W |
| Lamp Wattage Technical | 25.0 W |
| Power Factor | 1 - |
| Voltage | 230-240 V |
| Lamp Current | 0.11 A |
| Dimmable | Yes |
| Starting Time | 0.0 s |
| Warm-up Time to 60% Light Outp | instant full light |

• Environmental Characteristics

| | |
|-------------------------------|--------|
| Energy Efficiency Label (EEL) | E |
| Energy consumption kWh/1000h | 25 kWh |

• Measuring Conditions

| | |
|-----------------|-------|
| Switching cycle | 4000X |
|-----------------|-------|

• Product Dimensions

| | |
|------------------|-------------|
| Overall Length C | 57 (max) mm |
| Diameter D | 25 (max) mm |

• Product Data



| | |
|-----------------------------|--|
| Order code | 924198244442 |
| Full product code | 924198244442 |
| Full product name | Appliance 25W E14 230-240V T25 CL OV 1CT |
| Order product name | App 25W E14 230-240V T25 CL OV 1CT |
| Pieces per pack | 1 |
| Packing configuration | 20 |
| Packs per outerbox | 20 |
| Bar code on pack - EAN1 | 8711500038715 |
| Bar code on outerbox - EAN3 | 8727900800784 |
| Logistic code(s) - 12NC | 924198244442 |
| ILCOS code | IBT/C-25-230/240-E14-25* |
| Net weight per piece | 10.500 gr |

PHILIPS

Dimensional drawing

Appliance 25W E14 230-240V T25 CL OV 1CT

| Product | C (Max) | D (Norm) | D (Max) |
|--------------------------------|---------|----------|---------|
| APP 25W E14 230-240V T25 CL OV | 57 | - | 25 |



E14



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, August 29
data subject to change