



2745

Headlamp

Pelican™ safety approved headlamps are designed for use in hazardous environments. It is not only Class I Div 1 approved but also is ultra compact and lightweight. Equipped with three LEDs, it produces up to 33 lumens and provides up to 40 hours of run time and offers multiple modes (high, low, flashing). The Pelican 2745 is available in two colors (yellow or black). Count on Pelican to bring you the best in lighting design and technology.

The new Pelican™ 2745 headlamp: Guiding you safely through the danger zone.

- Built Pelican tough
- Hands-free design
- Comfortable Cloth Strap
- Safety Certified - Class I, Division I



DIMENSIONS

Length	2.25" (5.7 cm)
---------------	----------------

MATERIALS

Body	Polycarbonate (PC)
O-Ring	Over-molded TPR
Lens	Polycarbonate (PC)
Shroud	Polycarbonate (PC)

COLORS

 Black	 High Visibility Yellow
---	--

LIGHT SPECS

Lamp Type	LED
------------------	-----

POWER

Battery Size	AAA
Battery Type	Alkaline
Battery Quantity	3
Batteries Included	yes
Volts	4.5v

WEIGHT

Weight With Batteries	3.3 oz (94 gr)
Weight Without Batteries	2.0 oz (57 gr)

SWITCH

Switch Type	Push Button
--------------------	-------------

Light Modes

High / Low / Flashing






CERTIFICATIONS

Class I, Division 1
IECEX ia
InMetro

OTHER

Minimum Pack

1

FL1 STANDARD	HIGH	LOW
	33 LUMENS	17 LUMENS
	20h 0mins	40h 0mins
	35m	25m
	309cd	155cd
	IP54	

ACCESSORIES



2748
Strapless Headlamp Adapter

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 09-17-21