

MG140

Product no.: U-145-1000-ESDN



Benefits

- › High Gasfilter volume
- › Electronic filter control with alarm function
- › Switch power supply 100 - 240 V
- › 4 wheels for easy movement
- › Variable Speed setting
- › Quick and simple installation
- › Quick and simple installation
- › The MG 140 is suitable for applications with a high demand of gas and particle filtration, e.g. soldering, adhesives, clean room work. It can be placed and be moved easily between different work places. Variable speed and alarm function for filter exchange can be set via the remote control.
- › Applications: Hand soldering, heavy duty and general soldering, gluing, cleaning, filling, fine dust



Technical Data

Dimensions L x W x H (mm)	350 x 335 x 655
Dimensions L x W x H (inches)	13.77 x 13.18 x 25.78
Weight (approx.) in kg	18
Voltage	110 - 240 V, 50/60 Hz
Power	100 W
Noise level (distance 1 m) dB(A)	< 50
Max. vacuum	2300 Pa
Capacity m ³ /h	140
Pre-filter	Pre filter mat class F7
Compact filter	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	2 workstations
RS232 interface (remote control)	---
USB port	---
WX-compatible	---