

Product Information

without engagement until placement of order

Supplier	Article description			Art. No. / EAN	Warranty
T.I.P. Technische Industrie Produkte GmbH Siemensstr. 17 74915 Waibstadt Tel.: 07263-9125-0 Fax: 07263-9125-25 www.tip-pumpen.de	Garden pump GPK 3600			30147	24 Months
	Master Box Information				
	Master Box dimensions in cm			weight (kg)	pack. Unit
	Width	Depth	Height	gross	(pcs.)
-	-	-	-	-	
Article Information					
Color Box dimensions in cm			weight (kg)	Qty.	
Width	Depth	Height	net / gross		
39,2	19,3	26,3	6,5 / 7,7	1	
Garden pump GPK 3600			quantity / pallet:		
			quantity / truck:		

Description:

Reliable starter unit with garden pump housing, on- and off switch, low weight.

Suitable for all areas of use of garden pumps.

Maintenance-free capacitor motor with thermal overload protection. Mechanical seal Ceramic / Carbon, Stainless steel motor shaft. The pump housing is made of impact resistant plastic, the hydraulic unit in Noryl.

Area of application:

Watering the garden, handling the irrigation system, for domestic purposes. These pumps are perfectly suited for direct irrigation.

Technical Data:

Nominal performance:	650 Watt
Delivery height max / pressure.:	40 m / 4 bar
Flow rate max.:	60 l/min / 3600 l/h
Suction height max.:	9 m
Pump housing:	Plastic, shock resistant
Pressure port:	33,25 mm (1",
Suction port:	33,25 mm (1",
Fluid temp. max.:	35 °C
Power cord:	1,5 m / H07RN-F
Number of sprinklers max.:	2



Approval marks:

